

Алматы (7273)495-231
 Ангaрск (3955)60-70-56
 Архангельск (8182)63-90-72
 Астрахань (8512)99-46-04
 Барнаул (3852)73-04-60
 Белгород (4722)40-23-64
 Благовещенск (4162)22-76-07
 Брянск (4832)59-03-52
 Владивосток (423)249-28-31
 Владикавказ (8672)28-90-48
 Владимир (4922)49-43-18
 Волгоград (844)278-03-48
 Вологда (8172)26-41-59
 Воронеж (473)204-51-73
 Екатеринбург (343)384-55-89

Россия +7(495)268-04-70

Иваново (4932)77-34-06
 Ижевск (3412)26-03-58
 Иркутск (395)279-98-46
 Казань (843)206-01-48
 Калининград (4012)72-03-81
 Калуга (4842)92-23-67
 Кемерово (3842)65-04-62
 Киров (8332)68-02-04
 Коломна (4966)23-41-49
 Кострома (4942)77-07-48
 Краснодар (861)203-40-90
 Красноярск (391)204-63-61
 Курск (4712)77-13-04
 Кургaн (3522)50-90-47
 Липецк (4742)52-20-81

Магнитогорск (3519)55-03-13
 Москва (495)268-04-70
 Мурманск (8152)59-64-93
 Набережные Челны (8552)20-53-41
 Нижний Новгород (831)429-08-12
 Новокузнецк (3843)20-46-81
 Ноябрьск (3496)41-32-12
 Новосибирск (383)227-86-73
 Омск (3812)21-46-40
 Орел (4862)44-53-42
 Оренбург (3532)37-68-04
 Пенза (8412)22-31-16
 Петрозаводск (8142)55-98-37
 Псков (8112)59-10-37
 Пермь (342)205-81-47

Казахстан +7(7172)727-132

Ростов-на-Дону (863)308-18-15
 Рязань (4912)46-61-64
 Самара (846)206-03-16
 Санкт-Петербург (812)309-46-40
 Саратов (845)249-38-78
 Севастополь (8692)22-31-93
 Саранск (8342)22-96-24
 Симферополь (3652)67-13-56
 Смоленск (4812)29-41-54
 Сочи (862)225-72-31
 Ставрополь (8652)20-65-13
 Сургут (3462)77-98-35
 Сыктывкар (8212)25-95-17
 Тамбов (4752)50-40-97
 Тверь (4822)63-31-35

Киргизия +996(312)96-26-47

Тольятти (8482)63-91-07
 Томск (3822)98-41-53
 Тула (4872)33-79-87
 Тюмень (3452)66-21-18
 Ульяновск (8422)24-23-59
 Улан-Удэ (3012)59-97-51
 Уфа (347)229-48-12
 Хабаровск (4212)92-98-04
 Чебоксары (8352)28-53-07
 Челябинск (351)202-03-61
 Череповец (8202)49-02-64
 Чита (3022)38-34-83
 Якутск (4112)23-90-97
 Ярославль (4852)69-52-93

<https://beckman.nt-rt.ru/> || bnh@nt-rt.ru

Роботизированные лабораторные станции Biomek i5



Роботизированная лабораторная станция Biomek i5 помогает автоматизировать дозирование жидкостей и оптимизировать рабочие процессы, тем самым экономя время сотрудников. Идеально подходит для лабораторий со средними и высокими потоками исследований.

- 25 позиций на рабочем столе
- 2 базовые модификации:
- с многоканальным (96 или 384) дозирующим модулем
- с модулем Span-8 с 8 независимыми каналами
- диапазоны дозирования:
- 0,5 – 1 000 мкл (многоканальный)
- 0,5 – 5 000 мкл (Span-8)
- манипулятор с боковым захватом
- возможность интеграции внешних устройств
- библиотека готовых методик

Технические характеристики роботизированной станции Biomek i5

Minimum Table Support Requirements	71x83cm(28x33in)
Pod and Tool Type	1µL - 300 µL 96-Channel Head; 5 µL -1200 µL 96-Channel head; 0.5 µL - 60 µL Multichannel-384 Head
Tip Type	T30_384; T25F_384; T50_384; T40F_384; T80_384; T40F; T80_LLS; T40F_LSS; T90; T50F; T90_LSS; T50F_LLS; T230; T230_LSS; T190F_LLS; T230_WB; T1070; T1020_WB
Operating System	Windows® 10

Software	Biomek software, SAMI EX scheduling software, Biomek PowerPack software, Biomek Method Launcher, DART 2.0 software
Display	22" controller screen
Operating Modes	Semi-automated, manual, controlled by operator
Autoclavable	No
Item Specifications Referenced	B87583

Biomek i5 Span-8 with Enclosure B87584

Minimum Table Support Requirements	71x83cm(28x33in)
Platform	Biomek i-Series
Pod and Tool Type	Span-8 Pod
Environmental Conditions	Up to 2000 m
Installation Category	II
Power Requirements	100-240 VAC, 50/60 Hz, 10 A
Operating System	Windows® 10
Software	Biomek software, SAMI EX scheduling software, Biomek PowerPack software, Biomek Method Launcher, DART 2.0 software
Display	22" controller screen
Operating Mode(s)	Semi-automated, manual, controlled by operator
Autoclavable	No
Material(s)	ABS Cover, Aluminum Chassis, Acrylic Panels
Finish	High-gloss paint, Hardcoat anodized coating
Weight	172 kg(379.2 lb)

Width	112 cm(44.1 in)
Depth	81 cm(31.9 in)
Height	112 cm(44.1 in)
Package Quantity	1
Temperature Range	10° C - 30°C
Humidity Restrictions	20%–85% (non-condensing) at 30°C

Biomek i5 Multichannel with Enclosure B87583

Minimum Table Support Requirements	71x83cm(28x33in)
Platform	Biomek i-Series
Pod and Tool Type	1µL - 300 µL 96-Channel Head; 5 µL -1200 µL 96-Channel head; 0.5 µL - 60 µL Multichannel-384 Head
Tip Type	T30_384; T25F_384; T50_384; T40F_384; T80_384; T40F; T80_LLS; T40F_LSS; T90; T50F; T90_LSS; T50F_LLS; T230; T230_LSS; T190F_LLS; T230_WB; T1070; T1020_WB
Environmental Conditions	Maximum altitude: 2000 m
Installation Category	II
Power Requirements	100-240 VAC, 50/60 Hz, 10 A
Operating System	Windows® 10
Software	Biomek software, SAMI EX scheduling software, Biomek PowerPack software, Biomek Method Launcher, DART 2.0 software
Display	22" controller screen
Operating Mode(s)	Semi-automated, manual, controlled by operator
Autoclavable	No

Material(s)	Aluminum Chassis, ABS Cover, Acrylic Panels
Finish	Hardcoat anodized coating, High-gloss paint
Weight	181 kg(399 lb)
Width	112 cm(44.1 in)
Depth	81 cm(31.9 in)
Height	112 cm(44.1 in)
Package Quantity	1
Temperature Range	10° C - 30°C
Humidity Restrictions	20%–85% (non-condensing) at 30°C

Biomek i5 Multichannel without Enclosure B87516

Minimum Table Support Requirements	71x83cm(28x33in)
Platform	Biomek i-Series
Pod and Tool Type	1µL - 300 µL 96-Channel Head; 5 µL -1200 µL 96-Channel head; 0.5 µL - 60 µL Multichannel-384 Head
Tip Type	T30_384; T25F_384; T50_384; T40F_384; T80_384; T40F; T80_LLS; T40F_LSS; T90; T50F; T90_LSS; T50F_LLS; T230; T230_LSS; T190F_LLS; T230_WB; T1070; T1020_WB
Environmental Conditions	Up to 2000 m
Installation Category	II
Sterile	No
Power Requirements	100-240 VAC, 50/60 Hz, 10 A
Operating System	Windows® 10
Software	Biomek software, SAMI EX scheduling software, Biomek

	PowerPack software, Biomek Method Launcher, DART 2.0 software
Display	22" controller screen
Operating Mode(s)	Semi-automated, manual, controlled by operator
Autoclavable	No
Material(s)	Aluminum Chassis, Acrylic
Finish	Hardcoat anodized coating, High-gloss paint
Weight	155 kg(341.7 lb)
Width	112 cm(44.1 in)
Depth	81 cm(31.9 in)
Height	104 cm(40.9 in)
Package Quantity	1
Humidity Restrictions	20%–85% (non-condensing) at 30°C

Biomek i5 Span-8 without Enclosure B87578

Platform	Biomek i-Series
Environmental Conditions	Up to 2000 m
Power Requirements	100-240 VAC, 50/60 Hz, 10 A
Software	Biomek software, SAMI EX scheduling software, Biomek PowerPack software, Biomek Method Launcher, DART 2.0 software
Material(s)	ABS Cover, Acrylic Panels, Aluminum Chassis
Finish	High-gloss paint, Hardcoat anodized coating
Temperature Range	10° C - 30°C

Mobile Workstation: i5

Platform	Biomek i-Series
Installation Category	II
Sterile	No
Autoclavable	No
Material(s)	Aluminum sheet metal
Finish	Cardinal White Powder Coat
Weight	150 kg(330.7 lb)
Width	122 cm(48 in)
Depth	81 cm(31.9 in)
Height	84 cm(33.1 in)
Package Quantity	1

А лматы (7273)495-231 А нгарск (3955)60-70-56 А рхангельск (8182)63-90-72 А страхань (8512)99-46-04 Б арнаул (3852)73-04-60 Б елгород (4722)40-23-64 Б лаговещенск (4162)22-76-07 Б рянск (4832)59-03-52 В ладивосток (423)249-28-31 В ладикавказ (8672)28-90-48 В ладимир (4922)49-43-18 В олгоград (844)278-03-48 В ологда (8172)26-41-59 В оронеж (473)204-51-73 Е катеринбург (343)384-55-89	И ваново (4932)77-34-06 И жевск (3412)26-03-58 И ркутск (395)279-98-46 К азань (843)206-01-48 К алининград (4012)72-03-81 К алуга (4842)92-23-67 К емерово (3842)65-04-62 К иров (8332)68-02-04 К оломна (4966)23-41-49 К острома (4942)77-07-48 К раснодар (861)203-40-90 К расноярск (391)204-63-61 К урск (4712)77-13-04 К урган (3522)50-90-47 Л ипецк (4742)52-20-81	М агнитогорск (3519)55-03-13 М осква (495)268-04-70 М урманск (8152)59-64-93 Н абережные Челны (8552)20-53-41 Н ижний Новгород (831)429-08-12 Н овокузнецк (3843)20-46-81 Н оябрьск (3496)41-32-12 Н овосибирск (383)227-86-73 О мск (3812)21-46-40 О рел (4862)44-53-42 О ренбург (3532)37-68-04 П енза (8412)22-31-16 П етрозаводск (8142)55-98-37 П сков (8112)59-10-37 П ермь (342)205-81-47	Р остов-на-Дону (863)308-18-15 Р язань (4912)46-61-64 С амара (846)206-03-16 С анкт-Петербург (812)309-46-40 С аратов (845)249-38-78 С евастополь (8692)22-31-93 С аранск (8342)22-96-24 С имферополь (3652)67-13-56 С моленск (4812)29-41-54 С очи (862)225-72-31 С таврополь (8652)20-65-13 С ургут (3462)77-98-35 С ыктывкар (8212)25-95-17 Т амбов (4752)50-40-97 Т верь (4822)63-31-35	Т ольятти (8482)63-91-07 Т омск (3822)98-41-53 Т ула (4872)33-79-87 Т юмень (3452)66-21-18 У льяновск (8422)24-23-59 У лан-Удэ (3012)59-97-51 У фа (347)229-48-12 Х абаровск (4212)92-98-04 Ч ебоксары (8352)28-53-07 Ч елябинск (351)202-03-61 Ч ереповец (8202)49-02-64 Ч ита (3022)38-34-83 Я кутск (4112)23-90-97 Я рославль (4852)69-52-93
Россия +7(495)268-04-70	Казахстан +7(7172)727-132	Киргизия +996(312)96-26-47		

<https://beckman.nt-rt.ru/> || bnh@nt-rt.ru